



Product information

RNA-hopper

Complete line

Hopper
BU-W



- Fillvolume from 5 to 200 Litres
- Tank and chute in stainless steel, outside brushed
- Belt FDA-convenient
- Adjustable raised face in stainless steel
- Curtain lock
- 3-phase motor





Technical details:

Hopper with 3-phase motor

Type	BU-W 5	BU-W15	BU-W25	BU-W50	BU-W100	BU-W200
max. Fillvolume in Litre	5	15	25	50	100	200
max. Fillweight(kg)	15	50	70	80	100	100
Belt speed	2m/min					
Nominal voltage	230/400 V	230/400 V	230/400 V	230/400 V	230/400 V	230/400 V
Current consumption (A)	0,37	0,37	0,37	0,37	0,37	0,37
Power (W)	90	90	90	90	90	90
Control:	We advise EBB 1ZDS					
Motorprotection with connection						
Accessories	Support stands					
Motorposition	The motorposition is right (in running direction) in the standarddesign					

Dimensions



Typ	L	A	B1	B2	H	C
BU-W 5	475	450	120	125	90	145
BU-W 15	475	450	120	250	205	145
BU-W 25	525	500	150	280	235	145
BU-W 50	825	800	250	380	235	145
BU-W 100	1025	1000	300	430	265	145
BU-W 200	1025	1000	300	430	470	145




Fig. shows motorposition left



Rhein-Nadel Automation GmbH

Reichsweg 19-42 • D-52068 Aachen

Telefon 0241 5109-0 • Telefon (Vertrieb) 0241 5109-159 • Fax 0241 5109-219

Email: vertrieb@rna.de • Internet: www.rna.de

Stand: 23.06.06